

OGM-25Q-Slim Slim Type Aluminum Body Electronic Presetable Oval Gear Flow Meter



OGM-25Q-Slim Electronic Oval Gear Flow Meter is designed for working together with our electric transfer pumps, with voltage DC12V, DC24V, and AC220V. One wire connecting the pump, to control pump to start or stop working, the other wire to get power supply according to pump voltage. The LCD display shows unit price, amount and liters. To operate the keyboard, you can set the unit price, and preset the desired volume or amount, once the wanted volume or amount dispensed, the pump will stop working automatically.

Technical Specification:

Model No	OGM-25Q-Slim
Body Material	Aluminum (Slim/Lighter Type)
Accuracy	±0.5%
Flow Range	20-120L/min
Inlet/Outlet	1"

OGM-25Q-Slim-P Slim Type Plastic Body Electronic Presetable Oval Gear Flow Meter



OGM-25Q-Slim-P Electronic Oval Gear Flow Meter is designed for working together with our electric transfer pumps, with voltage DC12V, DC24V, and AC220V. One wire connecting the pump, to control pump to start or stop working, the other wire to get power supply according to pump voltage. The LCD display shows unit price, amount and liters. To operate the keyboard, you can set the unit price, and preset the desired volume or amount, once the wanted volume or amount dispensed, the pump will stop working automatically. **(It can be used for liquid of Ad-blue)**

Technical Specification:

Model No	OGM-25Q-Slim-P
Body Material	Plastic (Slim/Lighter Type)
Accuracy	±0.5%
Flow Range	20-120L/min
Inlet/Outlet	1"

OGM-25Q-Slim-SS Slim Type Stainless Steel Body Electronic Presetable Oval Gear Flow Meter



OGM-25Q-Slim-P Electronic Oval Gear Flow Meter is designed for working together with our electric transfer pumps, with voltage DC12V, DC24V, and AC220V. One wire connecting the pump, to control pump to start or stop working, the other wire to get power supply according to pump voltage. The LCD display shows unit price, amount and liters. To operate the keyboard, you can set the unit price, and preset the desired volume or amount, once the wanted volume or amount dispensed, the pump will stop working automatically. **(It can be used for liquid of Ad-blue)**

Technical Specification:

Model No	OGM-25Q-Slim-SS
Body Material	Stainless Steel (Slim/Lighter Type)
Accuracy	±0.5%
Flow Range	20-120L/min
Inlet/Outlet	1"